



GE CT Systems Remanufactured GE CT Scanners

Remanufactured GE CT scanners from Huestis Medical make premium diagnostic imaging systems affordable for any size treatment facility. CT is the latest addition to our renowned line of remanufactured systems from the very best names in imaging. These thoroughly remanufactured units are supplied with all necessary electrical, mechanical, and cosmetic upgrades for crisp imaging and like new operation. And they're guaranteed to deliver performance and safety features that meet or exceed original manufacturer's specifications.

Features

Mechanical Systems

- The system is dismantled and undergoes a thorough steam cleaning of all non-sensitive components.
- The system is inspected for structural imperfections and fatigue followed by replacement of worn/ unacceptable components.
- All motors, electrical switches and cooling fans are tested and replaced or rebuilt as necessary.
- All locks, detents and gears are inspected/ replaced as necessary.
- All bearings and track surfaces are inspected and replaced or repaired as required.

X-Ray and Electrical Controls

- The X-ray control is internally and externally cleaned with a non-destructive agent.
- All switch decks, tap switches relays and controls are tested and replaced as necessary.
- Any nonstandard wiring/ specialized modifications are removed and unit is restored to original specifications.
- All meters, indicators, lamps, controls and knobs are tested, inspected/ replaced as necessary.
- New CRT's installed in all monitors.
- Upgrades and enhancements are performed to current specifications.

Generator System


- The high voltage transformer is inspected for cable well integrity, oil purity, rectifier mounting and interlock switching integrity.
- All high voltage cables, worn wiring harnesses/ connectors are replaced.
- All defective components including switches, controls, and indicators are replaced.

Cosmetic Remanufacturing

- The system undergoes our refinishing process consisting of Kondar primer surfacing then applications of color coat with current GE type finish.
- The system is then reassembled for pre-staging and calibration.
- Any cabling subjected to flex breaking is replaced.
- Trim hardware is replaced as necessary.
- The system is completely assembled and prestaged for component compatibility, operational functions and calibrated to OEM specifications.

Added Features

- DICOM-3 interface.
- Systems shipped with flat table tops.
- Select Huestis Medical wiring harnesses.
- Optional laser systems.



Remarkable Remanufacturing

We supply all necessary electrical, mechanical, and cosmetic upgrades for crisp imaging and like new operation.



Excellent Imaging Performance

Guaranteed to deliver performance and safety features that meet or exceed original manufacturer's specifications.

HUESTISMEDICAL

Huestis ARI, 597 Winthrop Street, Taunton, Massachusetts 02780-2166 USA
508 824-8628 • 800 333-6070 • Fax 508 824-8629 • www.huestismedical.com

ISO9002
REGISTERED